



Save as PDF



**2380 LED Flashlight**



**INSTANT SPOT TO FLOOD.**

A dual purpose tactical light with flood and spot light capabilities: A wide light beam illuminates your work area and a focused light beam will light-up long trails. Our sophisticated slide beam technology instantly alters the beam distance from spot to flood and vice versa. Built-in battery level indicator ensures you will not be left in the dark.

The compact size (16.4 cm / 6.44"), ultra bright 159 lumen output, and aerospace grade aluminum body equal high performance in a small package. Built Peli tough and with guarantee of excellence, the new 2380 LED Light with slide beam technology gives you the lighting you need, when you need it.



**2380 LED Flashlight  
ANSI FL1 Specifications**

<b>LIGHT SOURCE.</b>	High LED
<b>BATTERIES</b>	2 AA Alkaline (Included)
<b>CHARGE TIME</b>	N/A
<b>VOLTAGE</b>	3
<b>LENGTH</b>	16.4 cm (6.44")
<b>WEIGHT W/ BATTERIES</b>	0.09 kg (3 oz.)
<b>WEIGHT W/O BATTERIES</b>	0.14 kg (4.9 oz.)

**LIGHT OUTPUT**  
**RUNTIME (hours/min)**  
**BEAM DISTANCE (meters)**  
**PEAK BEAM INTENSITY (candela)**

FL 1 STANDARD	High	Low
	3h 15m	
	149m	56 m.
	5579cd	779cd

**Materials**

Body	Lens	Shroud	Switch Type
Aluminum with Type II Anodized	PC	Aluminum with Type II Anodized	Push button On/Off tail switch
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
High Carbon Steel	N/A	EPDM	No

**Configuration**

Cat. #	Description
2380	2380 LED Flashlight

**2380 LED Flashlight Accessories**

Cat. #	Description
2322YW	Traffic Wand (Yellow)
2322OR	Traffic Wand (Orange)
2377	Cordura® Holster
1916	Break-away Safety Lanyard