

# PLC-BSC- 24UC/21HC

Order No.: 2967785



14 mm PLC-HC basic terminal blocks with screw connection method,  
input voltage 24 V AC/DC (without relay or optocoupler)

## Commercial data

EAN	4017918174187
Pack	10 pcs.
Customs tariff	85364190
Weight/Piece	0.05794 KG

## Product notes

WEEE/RoHS-compliant since:  
10/18/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### Input data

Nominal input voltage $U_N$	24 V AC/DC
Status display	LED
Protective circuitry	Bridge rectifier

---

**Output data**

Compatible components	Miniature relay, REL-MR-24DC/21HC
-----------------------	-----------------------------------

**Connection data**

Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3

**General data**

Length	80 mm
Width	14 mm
Height	94 mm
Color	green
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Mounting position	Any
Assembly instructions	In rows with zero spacing

**Certificates / Approvals**

Certification

CUL, CUL Listed, GL, GOST, UL, UL Listed

---

**Address**

PHOENIX CONTACT UAB  
Svitrigailos Str. 11b  
03228 Vilnius, LITHUANIA  
Phone +370 5 2106321  
Fax +370 5 2106324  
<http://www.phoenixcontact.lt>



© 2009 Phoenix Contact  
Technical modifications reserved;