


SPECIFICATIONS	
CONNECTOR HOUSING MATERIAL/PLATING	BRASS/NICKEL
GASKET	FLUOR RUBBER
PROTECTION CLASS	IEC IP65
TEMPERATURE RATING	-40°C to +125°C (-40°F to +257°F)



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC <i>High Technology Sensors and Automation Controls</i> 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1. 2. 3. 4.				DRFT JMS	DATE 06/16/97	DESCRIPTION CK-CC	
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DSGN	SCALE 1=1.0	IDENTIFICATION NO. U0103-1	
FINISH		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT MILLIMETERS		REV A	
A UPDATE PART, NOTES, NEW FORMAT		IK 01/30/01 T4381		DO NOT SCALE THIS DRAWING		FILE: U0103-1	
REV	DESCRIPTION	BY	DATE	ECO NO.	SHEET 1 OF 1		

A	UPDATE PART, NOTES, NEW FORMAT	IK	01/30/01	T4381
REV	DESCRIPTION	BY	DATE	ECO NO.