



TRA Series - Right Angle PC Mount

Right angle surface mount Mini-XLR connectors

Materials

- Housing: Thermoplastic
- Contacts: Brass, tin-plated
- Nut and Washer: Brass, nickel-plated

Electrical

- Current Rating: 5A for 3-6 pins, 3A for 7 and 8
- Contact Resistance: 10 m Ohm max.
- Insulation Resistance: 100 m Ohm min.
- Dielectric Withstanding Voltage: 250VAC

Mechanical

- Life: 2,000 cycles