



Issue	Description	Date
A	新图	2015/05/29



WIRING:

PIN1	WHITE	PIN1	PIN17	BLUE	PIN17
PIN2	RED	PIN2	PIN18	VIOLET	PIN18
PIN3	DRAIN	PIN3	PIN19	DRAIN	PIN19
PIN4	WHITE	PIN4	PIN7	ORANGE	PIN7
PIN5	BROWN	PIN5	PIN15	YELLOW	PIN15
PIN9	ORANGE	PIN9	PIN6	WHITE	PIN6
PIN10	PINK	PIN10	PIN8	BROWN	PIN8
PIN11	DRAIN	PIN11	PIN14	RED	PIN14
PIN12	GREEN	PIN12	PIN16	GREEN	PIN16
PIN13	WHITE	PIN13	Shell	BRAID	Shell
PIN20	BLUE	PIN20			
PIN21	YELLOW	PIN21			
PIN22	DRAIN	PIN22			
PIN23	GRAY	PIN23			
PIN24	BLACK	PIN24			



NOTES:

- 100% TEST OPEN.BSHORT.BMISWIRE
- CONTACT RESISTANCE:5 OHMS.
- INSULATION RESISTANCE:5M OHMS
- HI-POT VOLTAGE:300V DC 0.01SEC.



L=10M/15M

G.						All Dimensions are Millimeters	Approved	Checked	Drawn	
F.						Unless Otherwise Specified Tolerances				
E.										
D.	PLASTIC	4	PVC	BLACK		0.5~6= ±0.1				
C.	SCREW	4	IRON	NI		6~30= ±0.3				
B.	BODY	2	PVC	BLACK		30~120= ±0.5				
A.	DVI(24+)	2	BRASS	NI		120~315= ±0.8	TITLE	DVI PLUG TO DVI PLUG (24+1)		
NO	Description	Unit	Materials	Finish/Color	PART NO.	Scale	Issue	A	CABLE	CH62AL 24# (7/0.2TA*1P+7/0.2TA+ALMY)*7C +7/0.2TA*1P+7/0.2TA*3C+AL+24*8/0.12TA OD:12mm