




FEMALE END VIEW		MALE END VIEW	SPECIFICATIONS	
			CONTACT CARRIER MATERIAL/COLOR	NYLON/BLACK
1 = GREEN 2 = RED/BLACK 3 = RED/WHITE		1 = GREEN 2 = RED/BLACK 3 = RED/WHITE	MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
			RATED CURRENT [A]	4.0 A
			RATED VOLTAGE [V]	250 V
			OUTER JACKET MATERIAL/COLOR	PVC/YELLOW
			CONDUCTOR INSULATION MATERIAL	PVC
			NUMBER OF CONDUCTORS [AWG]	3x22 AWG
			TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
			PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP67, IP68, IP69K



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:

1. "*" DESIGNATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

D	DRAWING PROCESSED AS PART OF ECO 33971		CBM	04/06/11	33971	SEE SPECIFICATIONS	FOR MORE INFORMATION			D
REV	DESCRIPTION		BY	DATE	ECO NO.			DO NOT SCALE THIS DRAWING	FILE: 777001112	

SOURCE DRAWING - FOR REFERENCE ONLY

TURCK INC
High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE
MINNEAPOLIS, MN 55441
1-800-544-7769
(763) 553-7300
(763) 553-0708 fax
turck.com