

**Ordering number C11811_ANNA-50-6-S**

Family	Anna-50-6	FWHM	11 degrees
Type	Lens array	Efficiency	90 %
LED	Oslon SSL 80	cd/Im	11.700
Color	Clear	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

Ordering number C11812_ANNA-50-6-M

Family	Anna-50-6	FWHM	20 degrees
Type	Lens array	Efficiency	88 %
LED	Oslon SSL 80	cd/Im	4.200
Color	Clear	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

Ordering number C11813_ANNA-50-6-W

Family	Anna-50-6	FWHM	26 degrees
Type	Lens array	Efficiency	87 %
LED	Oslon SSL 80	cd/Im	2.400
Color	Clear	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Anna-50-6 series

last update 25/10/2012



GENERAL INFORMATION

- Product series especially designed & optimized for Oslon SSL 80 series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

