

Professionally approved products.

Datasheet

VGA Splitter (8 Port)

RS Stock number 783-9864



Short Description	8 Port VGA Splitter, 450Mhz, up to 65Mtr
Full Description	<p>The NLKVS-range of Video Splitters are designed for desktop use, supplied in a durable, compact metal housing. The splitters duplicate and boost the input signal to 2, 4 or 8 VGA, SVGA or Multi-sync Monitors, with a signal rate of 450 Mhz. Video Splitters are ideal for applications such as tradeshows, business meetings and demonstrations. These products are independent of software and other than cables and Monitors, no additional hardware is required.</p>
Extra Information	<p>Specification 250 - 450Mhz Video Bandwidth 8 Port Supports up to 2048 x 1536 Resolution Supports DDC, DDC2 & DDC2B(Port 1 only) Duplicate one signal input to multiple outputs Ability to be cascaded Effective transmission distance: 65 Mtrs Power saving mode Metal Case</p> <p>Contents 1 x Video Splitter 1 x Power Supply 1 x User Manual</p>