

Specifications for BMP41/BMP51/BMP53 Labelmaker Tape

Adhesive	Permanent Acrylic
Application	Indoor & Outdoor Grade Facility & Safety Identification
Article No.	131594
Brady Material No.	B-595
Material Type	Vinyl
Colour	White on Blue
Finish	Gloss
Laboratory Application	Well Plates; General Identification
Max. Service Temp. °C	82
Order Reference	MC1-1000-595-BL-WT
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Continuous
Size - Length (m)	7.62
Size - Width (mm)	25.40
Total Qty per Pack	1 Label(s) / Box
Industry	Data & Telecommunications; Electrical; Facility & Safety Industry; Process
Min. Application Temp. °C	-18
Min. Service Temp. °C	-40
QTY. per Row	1
Thickness (mm)	0.1