






1	2	3	4	5
---	---	---	---	---



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL

INSULATOR: PBT

COLOR: BLACK

CONTACT MATERIAL: COPPER ALLOY

CONTACT TYPE: STAMPED

CONTACT PLATING: GOLD

QUALITY CLASS: 3 AS PER CECC 75 301-802

PITCH: 2.54MM

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 125°C

FLAMABILITY RATING: UL94-V0

COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 3A

WORKING VOLTAGE: 250V AC

INSULATOR RESISTANCE: >1000 mOHM

DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/MN

CONTACT RESISTANCE: 20 mOHM MAX

STANDARD

⚡ CERTIFIED: E323964 / MODEL N° 613-218

SOLDERING

WAVE PROCESS ONLY


PACKAGING

TRAY

DIMENSION

A= 2.54 x (NB. PIN / 2-1)

B= 2.54 x (NB. PIN / 2) + 0.5

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15				
				APPROVAL: RJ	UNIT: MM	DESCRIPTION: 2.54MM DUAL SOCKET HEADER		SIZE	
I	28-AUG-14	DIMENSION	AS		SCALE:			A4	
H	08-APR-13	DIMENSION	AR		SHEET: 1/2	WERI PART NO: 613 0xx 218 21			
REV	DATE	FILE	BY		DRAW: PEARL				