



Datasheet

ENGLISH

Stock No: 564-475

RS Pro Telephone Slide Filament Indicator Lamp, Clear, 30 V, 40 mA, 6000h



Product Details

T5.5 Telephone Slide

Filament lamps will perform to specification and give optimum life when:

- They are powered at the rated voltage from a stabilised 50 Hz AC supply.
- Ambient temperature is in the range 20°C to 25°C.
- No mechanical vibration is present.

Deviations from these criteria have a significant effect on lamp life, particularly with low current filaments (<80mA).

Power from a DC supply at the rated voltage can reduce the listed life by up to 50%.

The effect of deviation from the rated operating voltage should be noted:

5% above will reduce lamp life by up to 50%.

5% below will significantly increase lamp life.

Power consumption may vary up to $\pm 10\%$ compared to the listed values at the rated supply voltage. Therefore particular care should be taken when a number of lamps are connected in series. In such applications it is recommended that the rated voltage be reduced by 10% to prevent premature failure of individual lamps.



ENGLISH

Specifications:

Voltage Rating	30 V
Lamp Base	Telephone Slide
Current Rating	40 mA
Diameter	5.4mm
Lamp Size	T5.5
Length	30 mm
Lens Colour	Clear
Luminosity	3.5 lm
Life Hours	6000h