

## Covering hood - HC-RBO 16 BU - 3247998


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Covering hood, Connection method: Bolt connection, Width: 54.8 mm, Height: 33 mm, Color: blue



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 6 pc                                                                                                    |
| Minimum order quantity               | 6 pc                                                                                                    |
| GTIN                                 | <br>4 046356 724470 |
| Weight per Piece (excluding packing) | 51.31 g                                                                                                 |
| Custom tariff number                 | 85472000                                                                                                |
| Country of origin                    | China                                                                                                   |
| Note                                 | Made to Order (non-returnable)                                                                          |

### Technical data

#### General

|                                         |      |
|-----------------------------------------|------|
| Color                                   | blue |
| Inflammability class according to UL 94 | V0   |

#### Dimensions

|                  |         |
|------------------|---------|
| Width            | 54.8 mm |
| Length           | 164 mm  |
| Height           | 33 mm   |
| Height NS 35/7,5 | 33 mm   |
| Height NS 35/15  | 40.5 mm |

#### Connection data

|                   |                 |
|-------------------|-----------------|
| Connection method | Bolt connection |
|-------------------|-----------------|

## Covering hood - HC-RBO 16 BU - 3247998

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141111 |
| eCl@ss 4.1 | 27141111 |
| eCl@ss 5.0 | 27141140 |
| eCl@ss 5.1 | 27141140 |
| eCl@ss 6.0 | 27141140 |
| eCl@ss 7.0 | 27141140 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC002498 |
| ETIM 5.0 | EC002498 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211827 |
| UNSPSC 7.0901 | 39121424 |
| UNSPSC 11     | 39121424 |
| UNSPSC 12.01  | 39121424 |
| UNSPSC 13.2   | 39121424 |