

ToLEDo Retro A60

ToLEDo RT A60 ST 806Lm E27 SL

0027131

Range features



PRODUCT OVERVIEW

Ordering number	0027131
Technology	LED
Light colour	Homelight
Energy class	A++
Average life (Rated) (h)	15000
Lamp shape	A60
Lamp finish	Satin
Dimmable	No
Cap/Base	E27
Type	ToLEDo Retro A60
EAN code	5410288271316
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Efficacy (Rated) (lm/w)	134.33
Watt (Nominal) (W)	6
Equivalent watt (W)	60
Voltage (V)	230-240

ToLEDo Retro A60

ToLEDo RT A60 ST 806Lm E27 SL

0027131

DATA TABLE

General data

Dry applications use only	Yes
Technology	LED
Ordering number	0027131
Energy saving lamp	Yes
Energy class	A++
Average life (Rated) (h)	15000
Average life (Nominal) (h)	15000
Lamp finish	Satin
Lamp shape	A60
Dimmable	No
Cap/Base	E27
Type	ToLEDo Retro A60
EAN code	5410288271316
Notes	Product available July 2015
Product name	ToLEDo RT A60 ST 806Lm E27 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
General application	Hospitality; Residential & Consumer
Intended purpose	No
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

Optical data

Light colour	Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	806
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	806
Adjustable chromaticity	No

ToLEDo Retro A60

ToLEDo RT A60 ST 806Lm E27 SL

0027131

Electrical data

kWh per 1000 hours burning time	6
Efficacy (Rated) (lm/w)	134.33
Watt (Nominal) (W)	6
Watt (Rated) (W)	6
Equivalent watt (W)	60
Voltage (V)	230-240
Drive current (mA)	52
Lamp power factor	0.5

Physical data

Lamp Length (mm) - C/L	105
Max. Lamp Diameter (mm) - D	60
Lamp dimension equal to filament lamp equivalent	Yes

ENERGY LABEL

