

Marker cards - SBS10:UNBEDRUCKT - 1007248

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Marker cards, Card, white, Unlabeled, Can be labeled with: Plotter, Perforated, Mounting type: Snap into tall marker groove, Snap into flat marker groove, For terminal block width: 10 mm, Lettering field: 6 x 10.1 mm



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 012854
Weight per Piece (excluding packing)	7.71 g
Custom tariff number	39207380
Country of origin	Germany

Technical data

Dimensions

Length (b)	6 mm
Width (a)	10.1 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 110 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	white
Material	cellulose acetate
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	250
Number of individual labels per row	10

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103

Marker cards - SBS10:UNBEDRUCKT - 1007248

Classifications

eCl@ss

eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410