



Sample photo

**Order symbol:** AL 232811  
**Product nbr:** 7011370  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074004246  
**EI. number:**  
Finland: 3423635  
Denmark: 8212004809  
Italy: 7321095  
Sweden: 2536337  
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with neoprene gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		280	230	110	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		11.0	9.1	4.3	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Material:</b>		Aluminium			<b>Certificates:</b> Fimko Gost R
<b>Base colour:</b>		RAL 7001			
<b>Cover colour:</b>		RAL 7001			
<b>Cover screws material:</b>		Stainless steel			
<b>Gasket material:</b>		Neoprene			
<b>Temperatures:</b>					
<b>Short term:</b>		-50 ... 140 °C			
<b>Continuous:</b>		-50 ... 80 °C			
<b>Short term:</b>		-60 ... 285 °F			
<b>Continuous:</b>		-60 ... 175 °F			
<b>Accessories:</b>					
AM 2328		Mounting plate			
ARH 2328		DIN-35 Mounting rail			
MRS 28541		Wall fastening lug (2 pcs)			
PH A & AH A/B		Hinge set			

