

General Information

Extended Product Type:	BJS9.5-10
Product ID:	1SNA173819R2200
EAN:	3472591738193
Catalog Description:	BJS 9.5 10 POLES Jumper Bars
Long Description:	BJS9.5-10 - Jumper Bars - 10 poles -- 9.5mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591738193
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	5.6 g
---------------------	-------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Gross Weight:	0.056 kg
Package Level 1 EAN:	3472591738193
Package Level 2 Units:	1000 piece

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJS
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 41 A
Spacing:	9.5 mm
Sub-Function:	Not Assembled Jumper bar
Sub-Function 2:	Screw
Suitable For:	M6/9.EE

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
------------------------------------	----------------------------------

Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

