







- ① ACCEPTS #4 SELF TAPPING THREAD CUTTING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.6 N-m MAX
- ② DATE CODE IN THIS LOCATION USING 5 DIGIT CODE
FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK, LAST DIGIT = DAY.
- ③ MATERIALS: GASKET - SILICONE
HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
- ④ HOUSING COLORS ARE MECHANICALLY KEYED TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
5. HEADER MATES TO PLUG ASSEMBLY 776286 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854





RECOMMENDED P.C. BOARD LAYOUT
FOR 1.57 THICK P.C. BOARD



SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0




SECTION A-A
OPTIONAL CONSTRUCTION IF PANEL
THICKNESS IS GREATER THAN 2.0



776276-2 & 1-776276-2
KEY LOCATION
SCALE 2:1

776276-1 & 1-776276-1 SHOWN

NATURAL	DURAGOLD	1-776276-2
BLACK	DURAGOLD	1-776276-1
NATURAL	TIN	776276-2
BLACK	TIN	776276-1
HEADER COLOR 	PLATING	PART NUMBER



DETAIL B
SCALE 10:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 21 JAN 2010 CHG. 2 MAR 2010 APVD. 2 APR 2010 D. STRAUSSER D. STRAUSSER D. STRAUSSER		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±1°		NAME ASSEMBLY, HEADER, 8 POSITION, VERTICAL, AMPSEAL WITH FLANGE SEAL	
		PRODUCT SPEC 108-1329 APPLICATION SPEC 114-16016		SIZE A1	
MATERIAL 		FINISH 		CAGE CODE 100779	
WEIGHT -		DRAWING NO. C-776276		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1
				REV B3	