

datasheet for MPB 1  
 article number: 930224100



<b>product description:</b>	order number: 930 224-100
<b>description:</b>	2 mm diameter miniature test socket, dimensions complying with DIN 41 649. Suitable for measuring and testing printed circuits during operation. Tin-plated sprung bronze contact spring. Test socket with horizontal and vertical connections.
<b>typ:</b>	MPB 1 schwarz/black
<b>system:</b>	2mm system
<b>order number:</b>	930 224-100
<b>color</b>	●
<b>other color versions:</b>	● ●
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>type of contact:</b>	socket (unsprung)
<b>type of termination:</b>	solder
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b> <a href="#">Please consider derating curve!</a>	6 A
<b>contact resistance:</b>	10 mOhm
<b>material</b>	
<b>contact material:</b>	bronze
<b>contact surface material:</b>	tin
<b>housing material:</b>	PC
<b>environmental conditions:</b>	
<b>temperature range:</b>	-20 °C to +60 °C
<b>inflammable class:</b>	
<b>housing (basic material):</b>	UL 94 HB
<b>drawing</b>	

