

Datasheet

RS Pro 4 SPST lever action dual-in-line switch

RS Stock No: **335-817A**



Product Details

RS Pro 4 SPST lever action switch is suitable for operating temperatures ranging from 20 to 80°C. This dual-inline switch withstands currents up to 100 mA at 50 V dc. It has gold plated contacts for optimum connectivity.

Features and Benefits

- Gold contacts, available in a choice of configuration
- Suitable for edge of board locations for timing, counting and coding circuits
- Changeover types have make-before-break contacts
- Non switching rating: Lever actuator; 100 mA at 50 V dc, piano actuator; 100 mA at 100 V dc
- Contact resistance: 50 MΩ

**Specifications:**

Actuator Type	Lever
Contact Configuration	SPST
Contact Current Rating	100 mA at 50 V dc
Contact Material	Gold
Maximum Operating Temperature	+80°C
Mechanical Life	10000 operations
Minimum Operating Temperature	-20°C
Mounting Type	Through Hole
Number of Positions	2
Operating Temperature Range	-20 to +80°C
Package Style	DIP
Voltage Rating	50 V dc