



Main

Range of product	Spacial CRN
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	300 mm
Enclosure nominal width	250 mm
Enclosure nominal depth	200 mm
Installation accessory type	Wall-mounting
Device composition	Lock 1 Door 1 Cable gland plate 1 Body 1
Door type	Plain
Mounting plate description	Without mounting plate

Complementary

Body type	Sides made from a single folded section Back welded with double profile forming a protected sealed area
Number of doors	1 front face
Door opening	Reversible 120 °
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Accessibility for operation	Front
Removable parts	Cable gland plate by screws Door by hinges
Material	Steel for body
Surface finish	Epoxy-polyester powder
Colour	Grey RAL 7035
Standards	IEC 62208
Product certifications	CUL UL

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------
