



Data-sheet FTP



FTP 140x54 Ø20 HL60
EAN

**Wheel centre made cast iron, tread made of Polyurethane, casted,
precision ball bearing,**

**Wheel diameter: 140 mm
Width of Tread: 54mm
Axle Hole Ø: 20 mm
Hub length: 60 mm
Temperature: - 20 / + 60 °C
Hardness of tread: Shore A 92
Dynamic Load capacity: 700 kg**