

Datasheet

RS Pro Thermostat, +10°C +315°C

RS Stock No: **436-0227**



Product Details

RS Pro thermostat has a operating temperature range of +10 to +315°C. This thermostat operates on the principle of the differential expansion of metals. It features compact steel body for durability. It comes with mounting bracket and clamp.

Features and Benefits

- Operates on the principle of differential expansion of metals
- Compact stainless steel body
- Supplied with mounting bracket and clamp
- Temperature adjustment via an external screw with working mechanism
- Contacts open on temperature rise



ENGLISH

Specifications:

Maximum Temperature	+315°C
Minimum Temperature	+10°C
Mounting Type	Surface Mount
Switch Function	Open On Rise
Material	Stainless Steel (Body)