



Product datasheet

ENGLISH

Conductive Neoprene Bench/Floor Mat

- Size: 1.2m x 0.6m
- Thickness: 2mm
- Colour: Black
- Manufactured from Neoprene Rubber
- Supplied with 10mm stud
- Solder Iron resistant
- Easy to Clean
- Low refelcting

RS code: 7873136



1) Bench applications

Test Results	Ω
Surface resistance R_s	3.3×10^7
Volume resistance R_v	8.5×10^6
Surface resistivity ρ_s	3.3×10^8
Volume resistivity ρ_v	1.3×10^4
Resistance to groundable point R_{gp}	7.7×10^7
Resistance point to point R_{p-p}	9.9×10^6

Conforms to IEC 61340-2-3

2) Floor Applications

Test Results	Ω
Resistance to groundable point R_{gp}	8.9×10^7
Resistance point to point R_{p-p}	1.3×10^7
Vertical resistance R_{vert}	2.2×10^6

Conforms to IEC 61340-4-1

