






LOC	DIST	REVISIONS				
		REV	LTR	DESCRIPTION	DATE	DWN APVD
AD	00	A1		REVISED PER ECO-11-004587	11MAR11	RK HMR

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
3. BECU CONTACT-PLATED WITH TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. PHOS. BRONZE CONTACT- PLATED WITH TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
5. MAXIMUM DIMENSION FOR I.C. SEATING PLANE.
6. HOUSING MATERIAL-GLASS FILLED THERMOPLASTIC, BLACK, 94V-0



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

	.900	9	.995	20	1-1825093-6
	.800	8	.895	18	1-1825093-5
	.700	7	.795	16	1-1825093-4
	.600	6	.695	14	1-1825093-3
	.300	3	.395	8	1-1825093-2
	.200	2	.295	6	1-1825093-1
	.900	9	.995	20	1825093-6
	.800	8	.895	18	1825093-5
	.700	7	.795	16	1825093-4
	.600	6	.695	14	1825093-3
	.300	3	.395	8	1825093-2
	.200	2	.295	6	1825093-1
CONTACT & FINISH	DIM C	B SPCS	DIM A	POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA	20APR2005		TE Connectivity				
DIMENSIONS: INCHES		CHK K.WRIGHT	-			NAME DIP SOCKET ASSY, CLOSED, DIPLOMATE, .300 CL, LEAD FREE			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-						
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	-						
MATERIAL		FINISH	APPLICATION SPEC	-		SIZE A1	CAGE CODE 00779	DRAWING NO. 1825093	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1		SHEET 1 OF 1	REV A1			