

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [180580-0004](#)
Status: **Active**
Overview: LED Array Holders, Dual-Ended Wire Trap
Description: LED Array Holder for 16.00 by 19.00mm COB, Circular Version, Gold (Au) Plating, One-Piece Design

Documents:

| | |
|---|--|
| Drawing (PDF) | Test Summary TS-180155-001 (PDF) |
| Product Specification PS-180580-004 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-180328-001 (PDF) | |



General

| | |
|----------------|---|
| Product Family | Solid State Lighting |
| Series | 180580 |
| Array Type | Nichia* |
| Beam Angle | N/A |
| Height | 4.10mm |
| Overview | LED Array Holders, Dual-Ended Wire Trap |
| Product Name | LED Array Holder |
| Type | Socket Assembly |
| UPC | 887191461083 |

Physical

| | |
|-----------------------------|-------------|
| Base Type | Direct Wire |
| Color Rendering Index (CRI) | N/A |
| Correlated Color Temp (CCT) | N/A |
| Lamp Type | Socket |
| Mounting Style | Screws |
| Net Weight | 8.570/g |
| Packaging Type | Tray |

Electrical

| | |
|-----------------------------|---------|
| Lamp Wattage - Maximum | N/A |
| Lumens | N/A |
| Voltage (Fixture) - Maximum | 600V DC |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|---------------|
| Application Specification | AS-180328-001 |
| Product Specification | PS-180580-004 |
| Sales Drawing | SD-180580-004 |
| Test Summary | TS-180155-001 |

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
 Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[180580Series](#)