



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-850 MHz
- 1.2 NOMINAL IMPEDANCE: 75 OHM
- 1.3 VSWR: 1.5 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C

6	NUT	BRASS	1	NICKEL 100μ" MIN.
5	CHASSIS	BRASS	1	NICKEL 100μ" MIN.
4	INSULATION II	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD
2	INSULATION I	TEFLON	1	NONE
1	BODY	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by _____ DATE: _____



DESCRIPTION		RCA JACK - F PLUG ADAPTER			
製 圖	DRAWN	TOLERANCE		品名	14-10-2 T.G.N
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT (750)
檢 査	CHECK	.XX	±0.1	DATE	05.20.10
	Arc	.XXX	±0.05	REV.	A-0
認 定	APPROVAL	.XX	±0.05	UNIT	mm(in)
	Lewis	ANGLE	±5°	SCALE	4:1
				DWG.NO.	14-0011