


Technical drawing of a mechanical part, showing a cross-section with dimensions: 2,1 ± 0,2, 5,0, 8,4, and 23,8.



- 1 Noryl (UL94-VI) Colore Nero (Black Colour).
- 2 Tolleranza non Cumulativa.
(Non-Cumulative Tolerance.)
- 3 PA 6.6 15% g.f. masterizzato ROSSO
(PA 6.6 15% g.f. masterized - RED)

4	284072-1	7,62	12,5			
2	284071-1	2,54	7,4			
22	280636	53,34	58,2			
15	280635	35,56	40,4			
12	280634	27,94	32,8			
10	280633	22,86	27,7			
9	280632	20,32	25,1			
8	280631	17,78	22,6			
6	280630	12,70	17,5			
4	280629	7,62	12,5			
2	280628	2,54	7,4			
N ^o Pos.	Part. Number	Dim. "A "	Dim. " B "			Mat.

FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION $\rightarrow$		
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA ALL INTERNATIONAL RIGHT RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
$\pm 0,3$		_____		_____	
ANGOLI (ANGLES) $\pm 2^\circ$		AMP AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)			
DIS. (DR.) Bessano 29 th 9- 86		DESCRIZIONE (DESCRIPTION) AMP MODU II Pin Housing, Single Row, Crimp Snap- In.			
CONT. (CHK) <i>Inten</i>		LOC. SIZE		REV.	
APP. (APP.)		IA3 C - (Master Dwg.)		H2	
		NUMERO (DWG NO.) 280628		SFOGLIO (SHEET) DI (OF) 1	