












	100 - 240 V~
	50 / 60 Hz
	2 x 2,5 mm ²
	-5°C / +45°C
	PIR/US
	300 lux
	15 mn
	45 m ²

												
230 V~	2000 W	8,5 A	1000 VA	4,3 A	10x(2x36 W)	4,3 A	500 VA	2,1 A	1000 VA	4,3 A	500 VA	2,1 A
110 V~	1000 W		500 VA		5x(2x36 W)		250 VA		500 VA		250 VA	

