

## Article

FTP 160 x 50 - 20



## Technical Data

Wheel diameter	160 mm
Width of Tread	50 mm
Dynamic Load capacity	770 Kg / daN
Static Load capacity	1925 Kg / daN
Axle Hole $\varnothing$	20 mm
Hub length	60 mm
Weight	2,882 Kg / daN
Temperature	- 40 / + 60 °C
Norm	EN 12533

## Description

Wheel centre made of lacquered cast iron, casted tread made of Polyurethane, precision ball bearing.

