



Save as PDF



**2750 LED Headlight**



Bright, compact headlight for harsh conditions with a night vision friendly red LED - the high output 2750 LED Headlight provides up to 100 lumens of illumination, flashing, and low light modes. The 2750 also preserves night vision with red LED light. Designed with weather resistant casings which also allows for fast and easy battery change.

Switch to the new 2750 Headlight from Peli.



**2750 LED Headlight  
ANSI FL1 Specifications**

<b>LIGHT SOURCE.</b>	High LED
<b>BATTERIES</b>	3 AAA Alkaline (Included)
<b>CHARGE TIME</b>	NA
<b>VOLTAGE</b>	4.5
<b>LENGTH</b>	5.7 cm (2.25")
<b>WEIGHT W/ BATTERIES</b>	0.13 kg (4.5 oz.)
<b>WEIGHT W/O BATTERIES</b>	0.06 kg (2.1 oz.)

**LIGHT OUTPUT**  
**RUNTIME (hours/min)**  
**BEAM DISTANCE (meters)**  
**PEAK BEAM INTENSITY (candela)**

FL 1 STANDARD	High	Low
	3h 45m	
	71m	49 m.
	1250cd	591cd

**Materials**

Body	Lens	Shroud	Switch Type
PC	PC	PC	Push button, high/low/flashing main white and low/flashing red
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
		Over-molded TPR	

**Configuration**

Cat. #	Description
2750	2750 LED Headlight

**2750 LED Headlight Accessories**

No accessories are currently available for this product