

Datasheet

RS Pro Green 30m Nylon Air Hose, -40 to +80°C, Application Various

RS Stock No: **483-4964**



Product Details

RS Pro nylon air hose is suitable for various applications with the temperatures ranging from -40 to +80°C. This cable in green colour, is anti-static.

Features and Benefits

- Ideally suited to applications requiring a more flexible nylon tube
- High flexibility even at very low temperatures
- Excellent abrasion resistance with a high durability to oil and petrol
- Extremely high impact and chemical resistance
- Maximum working pressure =<12.5 bar
- 30 m coils

**Specifications:**

Application	Air Brake, Fuel & Lube Applications, Industrial & Automotive Production Lines, Instrumentation & Secondary Air Systems
Colour	Green
Hose Inside Diameter	4 mm
Hose Outside Diameter	6 mm
Length	30 m
Material	Nylon
Maximum Operating Pressure	24 bar
Maximum Operating Temperature	+80°C
Minimum Operating Temperature	-40°C
Special Features	Abrasion Resistant
Wall Thickness	1 mm
Bend Radius	35 mm
Burst Pressure	Minimum of 72 bar