

Cable binder base - WT-BASE R HF 8 - 3240711


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Image shows WT-R HF 4.8x200 version

Cable binder base, for cable binders of up to 8 mm, with molded body-bound rivet, 6.5 mm drilling diameter, for material thicknesses up to 3 mm

Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 704281
Weight per Piece (excluding packing)	1.04 g
Custom tariff number	39269097
Country of origin	Taiwan

Technical data

Dimensions

Length (b)	10 mm
Height	18.5 mm
Width (a)	20.5 mm
Hole diameter	6.50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 60 °C

General

Color	transparent
Type	Fixing
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA 6.6

Cable binder base - WT-BASE R HF 8 - 3240711

Classifications

eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703