



Pioneer S

This full body harness has a rear attachment point and is adjustable both on the shoulders and the leg straps therefore adding considerable comfort and variable sizing. Conforms to EN 361 This harness is ideal for use in boom type elevated working platforms / cherry pickers. Used with an adjustable restraint lanyard it will prevent the user from over reaching and potentially falling. This basic harness can also be used in most other work at height applications.

1. Rear attachment point for fall arrest and restraint. Rear dorsal plate slides upwards helping the user remain upright after a fall.
2. Support strap gives the user extra comfort and support in the event of a fall.
3. Made from 44 mm polyamide webbing offering unrivalled strength, exceeding the minimum requirements required in the European standards.
4. Adjustable leg, shoulder and chest straps allows comfortable fitting for different sized people.
JSP Recommendation - JSP Fall Arrest harnesses should be used in conjunction with an appropriate and suitable JSP energy absorbing lanyard or other compatible JSP fall arrest devices.

Product Code Description

Pioneer S	FA8050	This full body harness has a rear attachment point and is adjustable both on the shoulders and th...
-----------	--------	--

