

**minifast® Quick Disconnect Adapters**

- Adapt to Standard *minifast* Cordsets
- Available w/NPSM or PG 9 Threads



Housing Style	Part Number	Specs	Features	Pinout	
	B2131-*M	Nylon 300 V, 4.0 A 3x22 AWG 70°C	Mates with 3-pin cordsets, 1/2 - 14NPSM Threads	1. Gn 2. Bn 3. Bu	
	B1131-*M	Nickel plated brass 300 V, 4.0 A 3x22 AWG 70°C	Mates with 3-pin cordsets, 1/2 - 14NPSM Threads		
	B2131-*M/S523	Nylon 300 V, 4.0 A 3x22 AWG 70°C	Mates with 3-pin cordsets, 1/2 - 14NPSM Threads	1. Bk 2. Bn 3. Bu	
	B2141-*M	Nylon 300 V, 4.0 A 4x22 AWG 70°C	Mates with 4-pin cordsets, 1/2 - 14NPSM Threads	1. Bn 2. Wh 3. Bu 4. Bk	
	B1141-*M	Nickel plated brass 300 V, 4.0 A 4x22 AWG 70°C	Mates with 4-pin cordsets, 1/2 - 14NPSM Threads		
	B1131-PG9-*M	Nickel plated brass 300 V, 4.0 A 3x22 AWG 70°C	Mates with 3-pin cordsets, PG 9 Threads	1. Gn 2. Bn 3. Bu	
	B1141-PG9-*M	Nickel plated brass 300 V, 4.0 A 4x22 AWG 70°C	Mates with 4-pin cordsets, PG 9 Threads	1. Bn 2. Wh 3. Bu 4. Bk	
	B1151-PG9-*M	Nickel plated brass 300 V, 4.0 A 5x22 AWG 70°C	Mates with 5-pin cordsets, PG 9 Threads	1. Bn 2. Wh 3. Bu 4. Bk 5. Gn	