

## HALOSTAR OVEN 10 W 12 V G4

HALOSTAR OVEN | Low-voltage halogen lamps with pin base for oven lighting



### Areas of application

- Baking ovens

### Product benefits

- Two to three times the luminous efficiency of conventional oven lighting
- Optimum halogen content for high temperatures
- Tempered pins for reliable contact at high temperatures
- Suitable for pyrolysis (permissible ambient temperature 450 °C)
- Contains no mercury



---

## Technical data

---

### Electrical data


Nominal wattage	10 W
Nominal voltage	12 V
Rated wattage	10 W
Power factor $\lambda$	1.00
Energy consumption	11 kWh/1000h

### Light technical data

Nominal luminous flux	140 lm
Color temperature	2800 K
Light color as per EN 12464-1	Warm White
Rated luminous flux	140 lm
Color rendering index Ra	100
Starting time	0.0 s

### Dimensions & weight

---



---

### Product line drawing

Diameter	10.0 mm
Length	33.0 mm
Overall length	31.0 mm
Light center length (LCL)	21.5 mm
Outer bulb	T10

### Colors & materials

Mercury-free	Yes
--------------	-----

# Product datasheet

## Lifespan

Nominal lamp life time	2000 h <sup>1)</sup>
Rated lamp life time	2000 h
Number of switching cycles	1000000 <sup>2)</sup>

<sup>1)</sup> Average lifespan at room temperature; higher temperature can reduce the lifespan

<sup>2)</sup> At 1 min on / 3 min off

## Additional product data

Base (standard designation)	G4
Footnote used only for product	Lamp suitable for oven with high temperature self cleaning (Lamps must be switched off! Max. ambient temperature 450 °C)/For use in shielded luminaires only

## Capabilities

Burning position	Any
Dimmable	Yes
Non-standard conditions	Oven
Not for household illumination	Yes

## Country specific categorizations

ILCOS	HSGT/C/UB-10-12-G4-10/21,5
Order reference	64418

---

## Country specific information

Product code	METEL code	SEG number	STK number	UK Org
4050300308081	OSRH64418	8326592	4730120	-

## Product datasheet

---

### Logistical Data

---

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4050300308081	HALOSTAR OVEN 10 W 12 V G4	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm <sup>3</sup>	5.20 g
4050300942339	HALOSTAR OVEN 10 W 12 V G4	Shipping carton box 40	121 mm x 107 mm x 144 mm	1.86 dm <sup>3</sup>	196.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### Disclaimer

---

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.