



FEMALE END VIEW



SPECIFICATIONS

CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	6-8mm
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)
PROTECTION CLASS	IEC IP67
WIRE TERMINATION	SCREW TERMINAL



**NOTE
PRELIMINARY
SPECIFICATIONS**

SOURCE DRAWING - FOR REFERENCE ONLY

ALL METAL SHIELDED FIELD WIREABLE CONNECTOR

RELATED DOCUMENTS		3RD ANGLE PROJECTION	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1.			ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT	GJA	DATE
2.		CONTACT TURCK FOR MORE INFORMATION		DSGN		SCALE
3.			SEE SPECIFICATIONS	UNIT OF MEASUREMENT		DESCRIPTION
4.		MILLIMETER [INCH]		CMB 8141-0		
MATERIAL		SEE SPECIFICATIONS		IDENTIFICATION NO.		REV
FINISH		SEE SPECIFICATIONS		U6112-01		A
A		DRAWING RELEASE		DO NOT SCALE THIS DRAWING		FILE: U6112-01
REV		DESCRIPTION		SHEET 1 OF 1		
BY	JBJ	DATE	03/26/04	ECO NO.		