

FEM6

ABB contact for United
States of America



General Information

Extended Product Type:	FEM6
Product ID:	1SNA107005R2500
EAN:	3472591070057
Catalog Description:	FEM6 End Sections Black
Long Description:	FEM6 - End Sections - Black - 2.8mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Sections

Ordering

EAN:	3472591070057
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	2.40 g
----------------------------	--------

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Gross Weight:	0.04800 kg
Package Level 1 EAN:	3472591070057
Package Level 2 Units:	1500 piece

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Additional Information

Ambient Temperature:	-5 ... +40 °C
Color:	Black
Function:	End Sections
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	FEM6
Product Name:	End Section
Spacing:	2.8 mm

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009
GOST Certificate: 1SND161005A1104
RoHS Information: 1SND230478F0202

Classifications

ETIM 4.0: EC000886 - Endplate and partition plate for terminal block
ETIM 5.0: EC000886 - Endplate and partition plate for terminal block
Object Classification Code: X

