

Fit-PC 2 Specifications

Size:	11.5 x 10.1 x 2.7 cm
Power usage:	9W Load (<1W Standby) 12V input Voltage tolerance 8-14V
CPU:	Intel Atom Z530 (1.6 GHz) / Z510 (1.1 GHz)
Memory:	Intel Atom 1.6GHz / 1.1GHz (Z530/Z510) 2GHz model from Q4 2010.
Hard Drive:	160GB 2.5" SATA HDD (except diskless models) SSD optional 8-16GB available. Drive is easily removable / replaceable.
Connectivity:	1000 BaseT Ethernet LAN 802.11 b/g/n WiFi Built-In 6 x USB 2.0 ports Mini-SDHC (bootable) slot IR Receiver
Operating Temperature Range	0 – 70 Deg C [Extended temp range available on Fit PC2i]
Video:	DVI Digital – up to 1920x1200 VGA available via Fit2 VGA converter. HD-capable 1080p
Audio:	S/PDIF 5.1 Digital Audio Microphone-in Line-in
Chipset:	Intel US15W
BIOS:	Phoenix BIOS
Weight:	330g

[See overleaf for details of Fit PC2 Accessories available from Fit PC UK](#)

Available Fit PC2 Accessories

(Please contact us for further details and pricing)

support@fit-pc.co.uk



7" USB Touch-Screen Monitor



Portable Battery + UPS



Fit PC2 VESA Mount + Secure Locking enclosure



7"-12.1" HDMI-input touch-screen monitors

(Available with and without enclosure).

support@fit-pc.co.uk | 0207 380 8153