




LOC	DIST	REVISIONS				
H	-	P	LTR	DESCRIPTION	DATE	DWN
		G2		REVISED PER ECO-11-005294	05APR11	RK
						APVD
						HMR

D


C

B

A



RECOMMENDED P.C. BOARD HOLE-LAYOUT



ACCESSORIES PREFIX "Z"	5	3,1 DIA. INSERT	2						2					
	5	INSERT WITH INNER THREAD 4-40 UNC		2						2				
	5	INSERT WITH INNER THREAD M3			2						2			
	4	FEMALE SCREWLOCK WITH 4-40 UNC				2						2		
	4	FEMALE SCREWLOCK WITH M3					2						2	
ITEM NR.	7	BOARDLOCK	2	2	2	2	2	2						
		DESCRIPTION OF ACCESSORY												

HOW TO ORDER

9 POS.-----> Z-338168-Y

PREFIX FOR ACCESSORIES }
BASIC PARTNR. }
SUFFIX FOR PLATING }

PLATING
SUFFIX "Y"

GOLD OVER NICKEL AS PER
PERFORMANCE LEVEL 2 (DIN 41652)
SOLDERPART :2,5µm TIN OVER NICKEL } -Y = -2

- } -

- 1 GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD;
WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.
- 2 CAVITY IDENTIFICATION AT FRONT SIDE ONLY.
- 3 PARTNUMBER AND DATE CODE.
- 4 SHELL HAS 2x2 GROUNDING SPRINGS; PITCH IS 3,6 mm
- 5 AIR AND CREEPAGE DISTANCES ACCORDING TO DIN 41652

ITEM NRS./MATERIAL :

- 1 SHELL : BRIGHT TINPLATED STEEL
- 2 HOUSING : GLASSFILLED POLYESTER,
COLOR : BLACK
- 3 CONTACTS : PH.BRONZE
(PLATING : SEE TABLE ABOVE)
- 4 FEMALE SCREWLOCK : TINPLATED STEEL
(INNER THREAD 4-40 UNC OR M3)
- 5 INSERT : TINPLATED STEEL (INNER THREAD 4-40
UNC OR M3 OR 3,1 DIA THRU-HOLE)
- 6 BRACKET : TINPLATED STEEL
- 7 BOARDLOCK : TINPLATED PHOSPHORBRONZE
- 8 POSTALIGNMENT PLATE : GLASSFILLED NYLON.
COLOR : BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. KESSLER	18 JAN 99	TE Connectivity	
DIMENSIONS: mm		CHK W.SOOMERS			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		NAME	
0 PLC ± -		PRODUCT SPEC		HD-20 SIZE 1 RIGHT ANGLE PLUG HEADER; MARK II+	
1 PLC ± -		APPLICATION SPEC		SIZE	CAGE CODE
2 PLC ± -				A2	00779
3 PLC ± -				DRAWING NO	
4 PLC ± -				C=338168	
ANGLES ± -		WEIGHT	-	RESTRICTED TO	
FINISH		CUSTOMER DRAWING		SCALE	
				NTS	SHEET
				1 OF 1	REV
				G2	