

## Hydroproof 2 - T5 Polycarbonate electronic ballast

Hydroproof 2 PC 254 T5 Eb

**0045593**



### Range features

- Body made from extremely resistant glass-reinforced polyester (SMC). Protection against chemicals (Please contact your local sales office for full listing). User-friendly and long lasting materials. Stainless steel closure clips ensure permanent pressure between diffuser and housing to guarantee IP rating.



### PRODUCT OVERVIEW

<b>Ordering number</b>	0045593
<b>EAN code</b>	5410288455938
<b>Certifications</b>	D-mark, ENEC
<b>Mount</b>	Ceiling surface
<b>Housing</b>	Glass fibre reinforced polyester
<b>Voltage (V)</b>	230
<b>Lamps</b>	2 x 54W T5 G5
<b>Colour</b>	Grey
<b>IP rating</b>	67
<b>IK rating</b>	8

## Hydroproof 2 - T5 Polycarbonate electronic ballast

Hydroproof 2 PC 254 T5 Eb

0045593

### DATA TABLE

#### General data

<b>Ordering number</b>	0045593
<b>EAN code</b>	5410288455938
<b>Certifications</b>	D-mark, ENEC
<b>Mount</b>	Ceiling surface
<b>Long description</b>	Body made from extremely resistant glass-reinforced polyester (SMC). Protection against chemicals (Please contact your local sales office for full listing). User-friendly and long lasting materials. Stainless steel closure clips ensure permanent pressure between diffuser and housing to guarantee IP rating.
<b>Product name</b>	Hydroproof 2 PC 254 T5 Eb
<b>Control gear availability</b>	Included
<b>Control gear mounting</b>	Integral
<b>Control gear type</b>	Electronic
<b>Environment</b>	Interior
<b>General application</b>	Car wash, Chemical industries, Mechanical industries, Technical rooms
<b>Housing</b>	Glass fibre reinforced polyester
<b>Special environment</b>	Clean room, Waterproof
<b>Sales pack quantity</b>	1

#### Optical data

<b>Distribution type</b>	Symmetric
--------------------------	-----------

#### Electrical data

<b>Voltage (V)</b>	230
<b>Lamps</b>	2 x 54W T5 G5
<b>Leading trailing edge</b>	No
<b>Number of heads</b>	1
<b>Total number of lamps</b>	2

#### Physical data

<b>Weight (kg)</b>	2.80
<b>Colour</b>	Grey
<b>Lamp included</b>	No
<b>IP rating</b>	67
<b>IK rating</b>	8
<b>Diffuser finish</b>	Prismatic
<b>Diffuser material</b>	Polycarbonate
<b>Emergency</b>	Without
<b>Single package dimensions (L x W x H) (cm)</b>	138.00 x 19.00 x 12.00
<b>Outer package dimensions (L x W x H) (cm)</b>	138.00 x 19.00 x 12.00

## Hydroproof 2 - T5 Polycarbonate electronic ballast


Hydroproof 2 PC 254 T5 Eb

0045593

### TECHNICAL DRAWINGS

Dimensions (mm) Weight (Kg)

Model T8	Model T5	L	W	H	F	Clips	Kg
1 x 18W	1x14/24W	702	102	108	500	6	1.9
1 x 36W	1x28W	1312	102	108	800	8	2.8
1 x 58W	1x35/49W	1612	102	108	1100	10	3.7
2 x 18W	2x14/24W	702	172	108	500	6	1.9
2 x 36W	1x54W /2x28W	1312	172	108	800	8	2.8
2 x 58W	1x80W /	1612	172	108	1100	10	3.7



### ENERGY LABEL

