

# Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sleeve housing, for double locking latch, height 76 mm, with screw connection, 1x Pg29, straight cable entry

The illustration shows version HC-D 50-TFQ-76/M 1 PG 21 G



## Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 10 pc   |
| GTIN                                 | <br>4 017918 038366 |
| Weight per Piece (excluding packing) | 341.56 g  |
| Custom tariff number                 | 85389099  |
| Country of origin                    | Germany   |

## Technical data

### Dimensions

|                         |                 |
|-------------------------|-----------------|
| Height                  | 76 mm           |
| Width                   | 56 mm           |
| Length                  | 82 mm           |
| Wrench size, union nut  | 37 mm           |
| External cable diameter | 18 mm ... 27 mm |

### Ambient conditions

|                                      |                   |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65              |
| Ambient temperature (operation)      | -40 °C ... 125 °C |

### General

|                      |                                     |
|----------------------|-------------------------------------|
| Note                 | For contact inserts HC-D25, A16/A32 |
| Type                 | D50                                 |
| Housing type         | Sleeve housing                      |
| Locking type         | For double locking latch            |
| No. of cable outlets | 1                                   |

# Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

## Technical data

### General

|                              |                     |
|------------------------------|---------------------|
| Cable exit                   | Straight            |
| Screw connection             | with                |
| Type of the screw connection | 1x Pg29             |
| Housing material             | Aluminum die-cast   |
| Housing surface material     | Powder-coated, gray |
| Cable gland material         | Nickel-plated brass |
| Cable seal material          | NBR                 |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

## Approvals

### Approvals

---

Approvals

EAC / GL

---

Ex Approvals

## Housing - HC-D 50-TFQ-76/M1PG29G - 1775813

### Approvals

---

Approvals submitted

---

### Approval details

EAC

GL

### Drawings

Dimensioned drawing

