



Model : LT-32HLF

Item	Specification		Item	Specification		
Size	Visible Diagonal	32 Inch	Aspect Ratio	16:9	○	
System	PAL/SECAM I, B/G, D/K	○	OSD	Halftone		
	SECAM L/L'	○		Enhanced(icon type)	○	
	NTSC 4.43(AV)	○		Menu	○	
Power	AC/DC Adapter	110/220V AC 50/60Hz		Multi Language	○	
	Power Consumption	150W		Program List/Edit	○	
	ST*BY Power Consumption	Below 3W	External Connection	AV*in	○	
Tuning	FS181 Program			AV*out	○	
	FVS 100 Program	○		S*Video in	○	
	Auto/Manual Programming	○		SCART(Full/Half)	2(Full/Half)	
Video	Progressive Scan	○		Headphone*out	○	
	PSM (Dynamic,Standard,Mild,Game, User)	○		Woofers*out	○	
	Digital Comb Filter	4H		DVI*in(D1)	○	
	Engine			PC*in(D*sub)	○	
	DCTI/DLTI	○		PC Audio*in	○	
Sound	Stereo(A2,NICAM)	○		User Convenient	Teletext(TOP/FLOF)	/○
	Equalizer	○	Teletext Page(Optional)		128	
	AVL(Auto Volume Leveller)	○	Caption(English)/V*Chip			
	Sound Output(RMS)	10W x 4	On/Off time			
	SSM (Flat,Music,Movie,Speech,User)	5MODE	PIP/DW/Scan		○	
Resolution	WXGA	1366 x 768	Optical		Q.View	○
					Sleep Timer	○
					ARC(Aspect Ratio Control)	○
					Auto AV	○
					DTV Built*in(Optional)	
				Viewing Angle	H:176 / V : 176	
				Luminance	450 cd/m ² (Typ.)	
				CR(Contrast ratio)	1000:1	

Dimensions(mm)			Weight(kg)	
SET SIZE (W*D*H)	SET SIZE with STAND (W*D*H)	BOX SIZE (W*D*H)	SET+STAND	Packing
933*112*503	993*230*562	1040*310*680	17.6+1.7 = 19.3	24.6

Response time : 16ms