

## General Information

<b>Extended Product Type:</b>	D6/8
<b>Product ID:</b>	1SNA215118R2500
<b>EAN:</b>	3472592151182
<b>Catalog Description:</b>	D6/8 Screw Clamp Terminal Blocks
<b>Long Description:</b>	Feed-through screw blocks The ABB Entrelec feed-through blocks offer the possibility to connect two or more wires on the same holder. All products can be mounted on standard DIN rail. Application: All electrical circuits mounted in cabinets or boxes.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Connection Type:</b>	Screw clamp
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	85369010
<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-A screw clamp
<b>Declaration of Conformity - CE:</b>	1SND225051U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>EAN:</b>	3472592151182
<b>Environmental Information:</b>	1SND220001E1002
<b>Flammability According to UL94:</b>	V0
<b>Gauge(s) of Form:</b>	A5
<b>IT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp
<b>Invoice Description:</b>	D6/8 Screw Clamp Terminal Blocks
<b>Minimum Order Quantity:</b>	50 piece
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	50 piece
<b>Package Level 1 EAN:</b>	3472592151182
<b>Package Level 1 Gross Weight:</b>	0.65 kg
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Length:</b>	220 mm
<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	81 mm
<b>Package Level 2 Gross Weight:</b>	20 kg
<b>Package Level 2 Height:</b>	300 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Units:</b>	1500 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 3 Units:</b>	36000 piece
<b>Pollution Degree:</b>	2
<b>Product Main Type:</b>	D6/8
<b>Product Name:</b>	Terminal Block

<b>Product Net Depth:</b>	41 mm
<b>Product Net Height:</b>	49.7 mm
<b>Product Net Weight:</b>	13 g
<b>Product Net Width:</b>	8 mm
<b>Product Packing Type:</b>	Box
<b>RMRS Certificate:</b>	1SND161007A1101
<b>Rated Cross-Section:</b>	6 mm <sup>2</sup>
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8 kV
<b>Recommended Screw Driver:</b>	4 mm
<b>RoHS Date:</b>	20050518
<b>RoHS Information:</b>	1SND230023F0208
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	Grey Screw clamp terminal blocks D 6/8 without central foot for DIN 3 rail only
<b>Spacing:</b>	8 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 0.8 N·m Manufacturer 1 N·m
<b>Wire Stripping Length:</b>	12 mm

