

Datasheet

RS Pro 50Ω Cable Mount SMP Connector Plug, Solder Termination Bulkhead Fitting Coaxial (RG405) Gold Limited Detent

RS Stock No: **878-2410**



Product Details

RS Pro cable mount SMP connector plug is designed for 50 Ω impedance applications. This bulkhead mount, limited detent plug connector features a gold plated brass body, solder terminal and mechanical interface in accordance with MIL-STD-348A. It is suitable for use with RG 405 coaxial cable and accommodates a maximum panel thickness of 3 mm.

Features and Benefits

- Gold plated
- Suitable for use with RG405 cable
- Limited detent connector

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Bulkhead	Yes
Cable Type	Coaxial (RG405)
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mating Type	Snap-On
Mounting Type	Cable Mount
Operating Frequency	18 GHz
Retention	Limited Detent
Size	Standard
Termination Method	Solder
Operating Temperature Range	-65 to +165°C