

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

P

F

ZONE

LTR

REVISIONS

DESCRIPTION

DATE

APPD

AF


50

F

REV PER 0710-0057-95

2/16/95

JR/JW



- 1 MATES WITH .032±.001×.187 TAB, PER NEMA DC-2
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .090-.160 DIA
- 4 DIMENSION DOES NOT INCLUDE TRIM BURR
- 5 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

HOUSING: NYLON, COLOR-BLUE TRANSLUCENT RECEPTACLE: #3 HARD BRASS TIN PL .000080 MIN THK		3-520412-2	
MATERIAL & FINISH		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± -	DR 11/2/88 P FORTNEY	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK 11/2/88 MS FEHER		
	APPD 11/2/88 K RANDOLH	NAME RECEPTACLE ASSY, ULTRA-FAST PLUS, LOOSE PIECE .187 SERIES, 16-14 AWG	
	APPD 11/14/88 T SHUTTER		
MATERIAL SEE TABLE	PRODUCT SPEC 108-2044	SIZE B	FSCM NO 00779
FINISH SEE TABLE	APPLICATION SPEC 114-2123	DRAWING NO 520412	
	WEIGHT -	SCALE 4:1	SHEET 1 OF 1