

INCANDESCENT LAMP 1.2 W, TRANSPARENT,
 RATED VOLTAGE AC/DC 24V, BASE BA 9S, LENGTH
 MAX. 28MM, BULB DIAMETER 10MM BULB
 DIAMETER 10MM RATED VOLTAGE AC/DC 24V
 TRANSPARENT






Figure similar

General technical data:		
Product designation		incandescent lamp
Type of light source		filament lamp
Color of the light source		clear
Mounting type		BA 9s
Product component		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
Type of voltage for actuation		AC/DC
Operating voltage		
• at AC		
— at 50 Hz Rated value	V	24 ... 24
— at 60 Hz Rated value	V	24 ... 24
• at DC Rated value	V	24 ... 24
Consumed current for rated value of supply voltage maximum	mA	55
Type of electrical connection		Miscellaneous

Mounting type

miscellaneous

Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other
 UL		 EG-Konf.	spezielle Prüfbescheinigung n Umweltbestätigung Bestätigungen

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB19020AY>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB19020AY>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB19020AY&lang=en

last modified:

20.07.2015