





- 1 CONTACTS DESIGNED FOR 28 AWG STRANDED OR 26,28, & 30 AWG SOLID WIRE.
- 2 AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 3 STANDOFFS: POSN 8 (2) STANDOFFS AS SHOWN. POSN 14-20 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN
- 4 .000005 MIN GOLD ON RIBBON CABLE TERMINATION AREA .000100-.000200 MATTE TIN ON SOLDER TAILS, ALL OVER .000050 MIN NICKEL.
- 5 HEIGHT AFTER TERMINATION IS (.253).
- 6 INDICATES NO 1 POSITION.
- 7 MOLDED PARTS: 94V-0 RATED THERMOPLASTIC, COLOR BLACK. CONTACTS: PHOS BRONZE



OBSOLETE	.900	9	1.088	.900	.950	19	20	5746613-5
OBSOLETE	.800	8	.988	.800	.850	17	18	-4
	.700	7	.888	.700	.750	15	16	-3
	.600	6	.788	.600	.650	13	14	-2
	.300	3	.488	.300	.350	7	8	5746613-1
	F	E	D	C	B	A	NO OF POSN	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ATTADIA - DOCKS CHK C. ROHDE APVD M. WALMSLEY	11-29-04 11-29-04 11-29-04	TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± -		108-40013	
		2 PLC ± -		APPLICATION SPEC	
MATERIAL		3 PLC ± .005		114-40005	
		4 PLC ± -		114-40005	
FINISH		WEIGHT		A1 00779 5746613	
CUSTOMER DRAWING		SCALE		NTS	
		SHEET		1 OF 1	
		REV		B1	