

Datasheet

RS Pro 2.2nF Ceramic Multilayer Capacitor 100 V dc $\pm 5\%$ NP0 dielectric MC max op. temp. +125°C

RS Stock No: **770-4285**



Product Details

RS Pro multi-layer ceramic capacitor has a capacitance of 2.2 nF. This 100 V dc rated capacitor includes NP0 dielectric. It is suitable for working temperatures up to +125°C.

Features and Benefits

- Full reel
- Surface mount
- Suitable for machine positioning

Specifications:

Capacitor Family	Multilayer
Dielectric	NP0
Dielectric Material Family	Ceramic
Mounting Type	Surface Mount
Terminal Type	Surface Mount
Capacitance	2.2 nF
Depth	1.25 mm
Dimensions	2 x 1.25 x 0.8 mm
Height	0.8 mm
Length	2 mm
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Temperature Coefficient	±30 ppm/°C
Tolerance	±5%
Tolerance (Minus)	-5%
Tolerance (Plus)	+5%
Package/Case	0805
Voltage	100 V dc
Application	Machine Positioning, Mobile Phones, Video & Tuner Designs, Decoupling
Package Type	Tape & Reel
Standards Met	RoHS Compliant; EIAJ-RC3402; EIA-RS198 & IEC PUB 384-10