

Housing - VC-MP-A3 - 1884429

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel mounting base, made of metal, powder-coated type 3, number of modules 4, cable screw connection Pg21



Key commercial data

Packing unit	5 pc
GTIN	4 017918 164454
Weight per Piece (excluding packing)	504.0 g
Custom tariff number	85389099
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	58 mm
--------	-------

Ambient conditions

Degree of protection	IP65/IP66/IP67
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	When using fiber optics, the bending radii of the cable manufacturers must be observed.
Type	VC3
Degree of protection	IP65/IP66/IP67
Locking type	Screw locking
Pg screw connection	none
Number of module slots	4
Housing material	Zinc die-cast
Housing surface material	Powder coating
Seal material	EPDM

Housing - VC-MP-A3 - 1884429

Technical data

General

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27371205
eCl@ss 5.1	27371205
eCl@ss 6.0	27371205
eCl@ss 7.0	27371205
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Accessories

Accessories

Marking label - VC-BZS WH - 1852875



Marker labels, unprinted, 5-section, for individual labeling with M-PEN or CMS system, white

Drawings

Housing - VC-MP-A3 - 1884429

Dimensioned drawing

