

SURFACE MOUNT. APPLIANCE INLET



16A 6P+E 6h 380-415V 50Hz 60Hz

COD. **245.1697-7**






OPTIMA-SEVEN is a range of industrial 7 poles plugs and socket outlets rated 16 and 32A Robust and safe industrial electrical plugs and sockets thanks to the use of high performance technopolymer enclosures and to the external cable gland with cable clamp

Notes

- Screw terminals
- Open threaded cable entry
- Threaded cap/cable sleeve included

TECHDATA

Synthetical description	SURFACE MOUNT. APPLIANCE INLET
Mounting version	SURFACE MOUNTING
Rated current	16A
Poles	6P+E
Hour position	6h
Rated voltage (range)	250-400V
Rated voltage	380-415V
Working frequency	60Hz 50Hz

Colour		RED
Protection degree		Watertight
Protection degree IP		IP66/IP67
Types of available outlets		ANGLED
Cable outlet		M25X1,5

STANDARDS AND LAWS

EN 60309-1 (1999)

[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

EN 60309-1/A1 (2007)

[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

EN 60309-1/A2 (2012)

[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

DIRECTIVE LOW VOLTAGE 2014/35/UE

[European Directives] Low Voltage Directive